

Diamond Light Source Introduction and Overview

Andy Dent

Physical Science Coordinator

Diamond Light Source Ltd



Diamond Light Source

Sited on Harwell Science and Innovation Campus

Largest scientific facility to built in the UK for over 40 years.

Opened for operations in January 2007

Phase I:


7 beamlines - 2007

Phase II:


+ 15 beamlines to be completed by 2012

Phase III:

+ 10 beamlines: approved, first 5 in design, 5 more under consideration







Machine Stats

Energy	3 GeV	
Beam current	300 mA 250 mA	Spec User Mode
σ_{x} σ_{y} $\sigma_{x'}$ $\sigma_{y'}$ Emittance	122.9μm 6.4μm 24.2μrad 4.2μrad	
- horizontal - vertical	2.7 nm rad 4-50 pm rad	~ 27 pm in User Mode
Lifetime at 300 mA	~ 18 h	but now operate top-up
Min. ID gap	5 mm	User Mode, depending on ID
Stability of beam size and divergence	2.5% (H), 7.5% (V) 0.5% (H), 1.7% (V)	No feedback Feedback, 1-100 Hz



Storage Ring









In-vacuum Undulators

6 out of the first 8 beamlines use in-vacuum undulators (unique for a new facility).

-20

The state-of the-art undulators are being developed in-house.





125


V Block Index

150







Beamline Programme



Beamline Programme







Thank you and enjoy the workshop

